



Thermal protection

TEMPICE 780

Temperature to -10°C | Wet environments

100% PVC



CHEMICAL PROTECTION
TYPE B

EN388



3221X

EN ISO 374-1



TYPE B
KPT

EN ISO 374-5



EN 511:2006



121

CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5

SPECIFIC ADVANTAGES



Thermal protection

- PVC specially designed for use in extreme cold (-10°C) while preserving the flexibility of the glove



Durability

- Good resistance to oils, greases and hydrocarbons



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Other industries
- Transport, logistics
- Fishing and Work at sea

APPLICATIONS

- Maintenance and work in cold stores
- Handling produce
- Handling of liquids at low temperatures (water, oil, hydrocarbons, etc.)



Thermal protection

TEMPICE 780

Temperature to -10°C | Wet environments

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
3 2 2 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance

EN 511:2006	COLD HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
1 2 1	
0-4 0-4 0/1	
	Water permeability
	Contact cold resistance
	Convective cold resistance

EN ISO 374-1	CHEMICAL RISKS
	K: Sodium hydroxide 40%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
TYPE B	

EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Jersey support, lined with woolen fleece
Exterior finish	Pebbled
Material	PVC
Colour.s	Orange
Length (cm)	30
European sizes	9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.7E+9 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	1.7E+11 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 48 pairs/carton
-----------	-------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/04/22/0794
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France

Edit 08/01/2025