

UN 38.3 Lithium Battery Test Summary

Cell, Battery or Product Model Number

Item Number:

Item Name: Li-ion Battery AHB472625PLT 3.7V 260mAh 1.0Wh

Cell, battery, or product manufacturer's contact information

Name: Kunshan SYNergy ScienTech Co.,Ltd

Address: No.688, Nanhe Road, Economic&Technical Development Zone, Kunshan, Jiangsu

City: KunShan

State: Jiangsu

ZIP: 215300

Country: China

Telephone: +86-512-57710688

E-mail: hmsong@synst.com.cn

Website: http://www.synst.com.cn

Test Laboratory

Name: The laboratory for UN38.3 of Kunshan SYNergy ScienTech Co.,Ltd

Address: 688# Nanhe Road Kunshan

City: KunShan

State: Jiangsu

ZIP: 215300

Country: China

Telephone: +86-0512-57710688-3411

E-mail: alice@synst.com.cn

Website: http://www.synst.com.cn

Cell or Battery Description

Cell or Battery: Battery

Physical Description (dimensions, appearance):

Cell or Battery Type: AHB472625PLT

Watt-hour rating or Lithium Content: 1.0Wh

Completed Cell or Battery Weight: Approx. 5.8 g

Silvery aluminum-plastics shell

Unique Test Report ID Number: UN18120402

Date of test report: 2018-12-05~2019-01-04

List of Tests Completed:

Yes	No		Pass	Fail	Additional Comments (or indicate compliance with other standards, e.g., Underwriters Laboratory):
Yes		Test T.1: Altitude simulation	Pass		Not Applicable
Yes		Test T.2: Thermal test	Pass		
Yes		Test T.3: Vibration	Pass		
Yes		Test T.4: Shock	Pass		Not Applicable
Yes		Test T.5: External short circuit	Pass		
Yes		Test T.6: Impact/Crush	Pass		
Yes		Test T.7: Overcharge	Pass		Sixth Edition
Yes		Test T.8: Forced discharge	Pass		

Signature with name and title of signatory as an indication of the validity of information provided:

Date:

实验室工程师 Laboratory Engineer

2019-11-1

UN38.3实验室