



### Shunt trip 230-415V AC 110-130V DC

MZ203

#### Technical Properties

Rated operational voltage Ue	230/415 V
Frequency	50/60 Hz
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Connection cross-sect. flexible cable	6mm <sup>2</sup>
Command voltage AC	230/415 V
DC control voltage	110/130 V
Operating temperature	-25 to 60 °C
Storage temperature	-40 to 80 °C
Number of modules	1