

Main

Range	TeSys
Device short name	VZ
Product or component type	Auxiliary contact block
Contacts type and composition	1 NC + 1 NO
Contact operation	Early-break 1 NC Late-make 1 NO
Product compatibility	V01C...V6C
Mounting location	Left Right

Complementary

Height	65 mm
Width	20 mm
Depth	48.5 mm
Net weight	50 g





Environment

Product certifications	UKCA[RETURN]CCC
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.624 cm
Package 1 Width	5.512 cm
Package 1 Length	8.961 cm
Package 1 Weight	40.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	60
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.51 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	960
Package 3 Height	75.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	58.272 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product