



Cut



Medium Duty

Economical solution for medium duty applications requiring high cut resistance, grip & oil-repellence performance in oily environment

- **Heightened grip:** Featuring a fully NBR-coated seamless liner with a rough palm, EDGE[®] 48-939 protective gloves offer a highly secure grip in oily environments, while protecting skin from injuries and oil contamination
- **Gauntlet design:** EDGE[®] 48-939 hand protection gloves' gauntlet extends oil repellent area and makes donning and doffing easy.
- **Enhanced defenses:** EDGE[®] 48-939 offers a high level of abrasion resistance and cut protection. In addition, the glove provides EN 407 level 1 contact heat protection, making it ideal for workers handling hot equipment, parts and objects.



Industries

- Aerospace
- Automotive
- Glass manufacturing
- Machinery and Equipment
- Metal fabrication
- Transportation
- Energy

Applications

- Machining / Stamping / Cutting
- Grinding
- Assembly of parts
- Maintenance
- Handling of glass sheets, sharp edged objects
- Handling materials with sharp or rough edges
- Handling sharp metal or objects

Key Features

- **NBR coating finish:** High grip in oily environment
- **Gauntlet design:** more oil repellent area and easy donning & doffing
- **Thermal resistance:** Ability to confidently handle hot components

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN 407



X1XXXX

EN388: 2016



4X43D

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE [®] 48-939	Finishing: Fully Dipped, Palm Coated, Rough Coating Material: Nitrile Liner Material: Polyester, HPPE, Spandex Cuff Style: Gauntlet	13	6, 7, 8, 9, 10, 11, 12	285 to 345mm / 11.22 to 13.58 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.