



Main

Range	Acti9
Product name	Acti9 Isobar B
Product or component type	Loose enclosure
Device application	Distribution
Provided equipment	1 DIN rail Door Plain front cover enclosure

Complementary

Enclosure mounting	Surface
Number of ways	34 (1P)
Number of horizontal rows	2
Enclosure material	Folded sheet steel: RAL 9001 epoxy powder coat
Height	484 Mm
Depth	138 Mm
Width	470 Mm

Environment

IP degree of protection	IP3x conforming to BS EN 60529
-------------------------	--------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 Cm
Package 1 Width	48.0 Cm
Package 1 Length	48.0 Cm
Package 1 Weight	9.443 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	24
Package 2 Height	112.0 Cm
Package 2 Width	100.0 Cm
Package 2 Length	120.0 Cm
Package 2 Weight	241.632 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	183

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : Commercialised
