




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #DT15-12PB-G003
HDR, 12P, BRK, ST, AU/NI/CU, B




TE Part #104809-6
07 MTE HDR SRST LATCH W/HLDWN




TE Part #5-338169-2
15P HDP20 PLUG ASSY



TE Part #1676970-7
RN 0603 59K 0.1% 10PPM CUT LENGTH



TE Part #1725761-1
KIT,SEATING TOOL, 1X4




TE Part #1879260-2
RP 2B 2K67 0.1% 15PPM 1K RL



TE Part #3-1879514-1
CRGH1206 1% 221R 0.5W



TE Part #3-1393480-3
V23529B1122C215=SUB D STIFTLEI



TE Part #826938-4
4P AMPMODU II STIFT LEI



TE Part #104809-4
05 MTE HDR SRST LATCH W/HLDWN

Documents

Product Drawings
35P MESSERLEISTE

English

CAD Files

Customer View Model
ENG_CVM_827254-1_2.3d_igs.zip

English

Customer View Model
ENG_CVM_827254-1_2.3d_stp.zip

English

Customer View Model
ENG_CVM_827254-1_2.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.