




mecalectro

Small linear solenoid for standard use – 8.M13.02.62 (Push)



Stroke: 9 mm

Force at beginning of stroke (FM: 100/25/5%):
1/3/12 N

Force at end of stroke (FM: 100/25/5%):
4/10/40 N

Power Consumption (FM: 100/25/5%):
6.5/23/102 W

Total mass: 160 g

Degree of protection / Energetic class: IP 00 / B
Standard supplies: 24Vcc

Possible supplies: From 6 to 220Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: various automations, positioning, multiple locks