



## MIDI 4-PP10

Blade Fuse, Midi (ATO, Norm), 4A, Pink

### Product Properties:

Release characteristic	Fast (F)
Rated voltage	32 V
Type of current	DC
Colour code	Other
Nominal voltage DC	32 V
Number of fuses	10 .
Model	Blade fuse
Max. current (I <sub>max</sub> )	4 A
Nominal current	4 A
Fuse type	Midi

### Dimensions:

Width	18.8 mm
MOQ	10 .
Unit	pck
Rated voltage	32 V
Length	18.7 mm

### Approvals:

### Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

## Other information:

<b>ETIM-Class</b>	EC002298 - Blade fuse
<b>ETIM-Release</b>	9.0
<b>Trademark</b>	NECORE
<b>Product Group</b>	Blade fuses - Pin-pac
<b>Search Description</b>	FLATSÄKRING, MIDI (ATO, NORM), 4A
<b>Alternative SKU</b>	MIDI4-PP10

## Logistic information:

<b>Barcode</b>	733117618642
<b>Country of origin</b>	SI
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	MIDI 4-PP10
<b>Taric code</b>	85361010
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.