

FEATURES

- Large and quick opening
- Handle Locks in both forward and reverse position
- Stainless steel rivets
- Body and linkage components are zinc plated to resist corrosion
- The clamps are self-arresting, they remain locked, resisting the force produced when machining components
- Heavy duty with 250kg holding force

RS PRO 21mm Toggle Clamp

RS Stock No.: 254-686



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This Push Pull Toggle Clamp from our own RS PRO brand offers the advantage of having a low profile, using side or end clamping and are most suitable for applications having a height restriction. With large power transmission and minimum operating effort, this toggle clamp gives you maximum clamping force to help you out in any job.

General Specifications

Type	Toggle Clamp
Application	Metalworking industry, wood and plastic industry

Mechanical Specifications

Jaw Opening	21mm
Nominal holding force	250Kg

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------





Dimensions:

