



ENGLISH

Datasheet

RS PRO Empty Fan Fan Tray

Stock No: 118-3285

1U, 19" EMPTY FAN TRAYS

These fan trays are offered without fans fitted to allow different types / configurations of fans to be fitted. These are offered as AC versions comprising the tray & front panel with IEC inlet & Neon fitted and as DC versions with the Molex Mini fit Jr. and 10mA LED fitted.

The fan trays are supplied with a rack fixing kit containing screws washers and cage nuts & and assembly leaflet.

Standard fan trays are designed to accept 119 x 119mm fans with a maximum height of 38mm whilst filtered fan trays are designed to accept fans of 119 x 119 with a maximum height of 32mm.

FEATURES:

- 1U integral height (to IEC 297-1)
- 70% open-area vent pattern
- Available in 3 or 6 fan sizes
- Available with115V & 230V AC input
- Available with 12, 24 & 48V DC input
- Available with silver (anodised) or black (painted) front panel

SPECIFICATIONS:

- 3 fan trays are 250mm deep, 6 fan tray are 350mm deep
- Material for tray is 1mm thick galvanised steel
- Silver front panel is 3mm thick Aluminium alloy anodized
- Black front panel is 3mm thick steel, black powder coated

Note: Depending on the chosen DC supply, the correct current limiting resistor must be fitted to the LED.

ORDERING INFORMATION:

Description	Voltage	Ordercode (Silver front)	
6-Fan Standard	230V AC	1183285	





