


Tooling NO.
MD4M TOOLING:980084
MD4F TOOLING:980085

REVISIONS			
DATE	LTR	DESCRIPTION	APVD



PIN ASSIGNMENT:

MD4 M	1	2	3	4	Shell
	Black	White	Red	Yellow	Drain
MD4 F	1	2	3	4	Shell

Specifications:

Temperature Range: -25°C To +85°C.
 Current Rating: 1A AC/DC
 Insulation Resistance: 50MΩ Min.
 Voltage Rating: 50V AC/DC
 Withstanding Voltage: 500V AC For 1 Min.



4	2.0	Mr	CABLE	Non-UL 28AWG 4C.+Drain+AL/Foil, Jacket Color: Black.	UNLESS OTHERWISE SPECIFIED TOLERANCE : X ±0.2 ANGLES : ±2° XX ±0.1 XXX ±0.05 NO INY SCALE DRAWING	TITLE Plug To Socket MiniDin Cable Assemblies			
3		KG	1-1487209-3	Molded PVC Color: Black.					
2	1	EA	6-1487178-1	MD4 Female, Contact: Gold Flash,Shell: Nickel Plated, Insulation: Black,PBT UL94V-0					
1	1	EA	6-1487178-4	MD4 Male, Contact: Gold Flash,Shell: Nickel Plated, Insulation: Black,PBT UL94V-0	DRAWN BY LINJEA	SIZE A UNIT MM	PART NO. 463-530	THIRD ANGLE PROJECTION 	PAGE 1 OF 1
ITEM	QTY	U/M	PART NO.	DESCRIPTION	CHECKED BY 	SCALE 1 : 1	DATE 08/27/2001	DWG NO. DEWP2001062703X0	ITEM NO. CM04FH04M28040066NM-01E