

PRODUCT-DETAILS

RHA 597 10m cable

RHA 597 10m cable Pluto safe encoder



General Information

Extended Product Type	RHA 597 10m cable
Product ID	2TLA020070R5900
EAN	7320500410905
Catalog Description	RHA 597 10m cable Pluto safe encoder
Long Description	Absolute encoder RHA 597, singel turn, 10m cable, hollow shaft, 12mm hole.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	90291000

Popular Downloads

Data Sheet, Technical Information	2TLC010001C0202
Instructions and Manuals	2TLC172006M0205
Marketing Video	2TLC010018N0201

Dimensions

Product Net Depth / Length	87 mm
----------------------------	-------

Product Net Height	58 mm
Product Net Width	58 mm
Product Net Weight	0.65 kg

Technical

Protocol Type	Pluto Safety Bus
Suitable For	Pluto AS-i v2 Pluto A20 v2 Pluto B20 v2 Pluto B22 Pluto B42 AS-i Pluto B46 v2 Pluto D20 Pluto D20 (Harsh Env) Pluto D45 Pluto D45 (Harsh Env) Pluto O2
Supply Voltage	24 V DC

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2TLC172014D0201
Environmental Information	2TLC172004D0201
Instructions and Manuals	2TLC172006M0205
RoHS Information	2TLC172009D0201

Classifications

Object Classification Code	B
ETIM 4	EC001486 - Rotary encoder
ETIM 5	EC001486 - Rotary encoder
ETIM 6	EC001486 - Rotary encoder
ETIM 7	EC001486 - Rotary encoder
eClass	V11.0 : 27270590
UNSPSC	39121527

Categories

Low Voltage Products and Systems → Control Products → Safety Products → Programmable Safety Controllers → Encoders

