

Rexel Secure X6 Cross Cut Paper Shredder

Rexel's range of Secure paper shredders are ideal for destroying your personal documents and sensitive information at home. The Secure X6 shredder machine shreds up to 6 sheets of A4 paper (80gsm) in one go through the manual feed slot into P-4 (4x40mm) cross cut pieces. This cross cut shredder is small and compact making it a perfect home shredder for use in a home office; it is also an ideal personal office shredder that fits conveniently under a desk. Designed for light to moderate use with a 10L bin capacity.



Attributes

- Shreds up to 6x A4 sheets (80 gsm) at once
- Cross cut (P-4 DIN security level)
- 10L (100 A4 sheets) bin capacity with a lift off shredder head. Transparent bin window to see when full.
- Quiet shredding <70 dBA
- Shreds staples and paper clips
- 3 minutes continuous run time
- Manual reverse / forward feature
- 2 year warranty, 2 year cutter warranty



Specifications

| | |
|---------------------------------------|------------------------------|
| Number | 2020122 |
| Colour | black |
| Dimensions (W x H x D) | 320 x 300 x 170 mm |
| Maximum Slot Entry Width (mm) | 220 |
| Run Time From Cold (min) | 3 |
| Shredded Particle Width mm | 4x40 |
| Security Level | P-4 |
| Cutting Capacity sheets (70gsm paper) | 7 |
| Cutting Capacity sheets (80gsm paper) | 6 |
| Container/collection volume in l | 10 |
| Shreds | Paper, Paper clips & Staples |
| Power consumption (W) | 100 |
| Noise Level (dBA) | 68 |
| Period of Warranty (Years) | 2 |
| Weight | 3300 g |
| Pallet quantity | 40 |
| EAN code | 5028252615167 |