



# Product data sheet

Power tools for trade & industry

Impact Wrench

## GDR 18V-220 C



The most compact Bosch Professional 18V impact driver

### The most important data

Battery voltage	18.0 V
Torque, max.	220 Nm
No-load speed	0-3,400 rpm

**Part Number** 0 601 9L6 001

## Technical data

### Technical data

Torque adjustment range, min./max., 1st level	0/100 Nm
Torque adjustment range, min./max., 2nd level	0/140 Nm
Torque adjustment range, min./max., 3rd level	0/220 Nm
No-load speed	0-3,400 rpm
No-load speed (1st level)	0-800 rpm
No-load speed (2nd level)	0-2,300 rpm
No-load speed (3rd level)	0-3,400 rpm
Torque settings	3
Weight excl. battery	1 kg
Torque, max.	220 Nm
Impact rate	4,000 bpm
Impact rate (1st level)	0-1,500 bpm
Impact rate (2nd level)	0-3,400 bpm
Impact rate (3rd level)	0-4,000 bpm
Battery voltage	18.0 V
Tool holder	1/4" Hex Uni
Packaging dimensions (width x length x height)	360 x 444 x 155 mm

**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Faster work progress thanks to powerful motor
- Optimised for convenience with one-handed bit insertion and two LED lights
- More control and versatility via three-speed/torque settings and adjustable screw modes

