

Product information

18V DRILL DRIVER 13MM LXT



DDF456Z

Voltage	18 v
Max. in wood	38 mm
Max. in steel	13 mm
Max Torque S/H	32/50 Nm
No Load Speed	H: 0 - 1500 / L: 0 - 400 rpm
Torque Settings	16
Battery Type	Lithium-ion
Vibration: Drilling	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Body only machine	1
Net weight	1.7 kg



- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Fully Compatible with 18V 4.0Ah Battery with 36 minute charge time.
- 4 pole motor.
- High comfort grips.
- Conveniently located push button for forward and reverse.
- LED job light with afterglow.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Metal gears
- Keyless chuck.
- Two speed gear box.

Details correct as of: 3-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com