

Datasheet

RS Pro Plain Stainless Steel Flat Head Machine Screws, M3 x 20mm

RS Stock No: **158-3360**



Product Details

RS Pro machine screw measuring M3 x 20 mm, is made of type 316 S16 plain A4 grade 18/8 stainless steel, which has higher level of corrosion resistance than A2 stainless steel. The flat head screw can be used at up to 300°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A4 grade 18/8 stainless steel (Type 316 S16) construction
- Higher level of corrosion resistance than A2 S/S
- Suitable for use up to 300°C
- Suitable for use in most food, medical, chemical, construction and electronic applications



ENGLISH

Specifications:

| | |
|----------------------|-----------------|
| Drive Type | Slot |
| Finish | Plain |
| Head Shape | Countersunk |
| Material | Stainless Steel |
| Length | 20 mm |
| Stainless Steel Type | 316 (A4) |
| Thread Pitch | 0.5 |
| Thread Size (Metric) | M3 |
| Head Diameter | 5.2 to 5.5 mm |
| Head Height | 1.65 mm |
| Slot Depth | 0.6 to 0.85 mm |
| Slot Width | 0.8 mm |
| Specification | DIN 963 |