



Main

Range	ClimaSys
Product name	ClimaSys CE
Product or component type	Air-air exchanger
Mounting type	Sides of enclosure
Cooling power	36 W power is obtained by multiplying specific power by DeltaT (Tex.t-Tint.)

Complementary

Flow rate	External circuit: 570 m3/h Internal circuit: 570 m3/h
Control type	Thermostat
Temperature setting range	5...60 °C
Ambient air temperature for operation	5...55 °C outside the enclosure:
Nature of the fluid	Air
Input voltage	230 V 50/60 Hz
[In] rated current	0.7 A
Power consumption in W	160 W
Height	External: 771 mm
Width	External: 316 mm
Depth	External : 103 mm
Net weight	10 kg
Noise level	62 dB conforming to EN/ISO 3746
Protection type	Thermal protection: T 1 A
Material	Steel
Colour	Grey (RAL 7035)

Environment

IP degree of protection	IP22 (external IP) IP55 (internal IP)
Product certifications	CE
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery
Standards	EN 60204-1 EN/ISO 12100 EN 60335-2-40 EN 60335-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins