

Internal / External Thread Files

- Restores damaged left or right-hand internal or external threads
- Also makes an ideal thread gauge
- Metric Thread Pitch: .80, 1.00, 1.25, 1.50, 1.75, 2.00, 2.50, 3.00
- Imperial UNC - UNF: TPI 11, 12, 13, 14, 15, 18, 20, 24

Part No.	Barcode	Type
SCMT70553	9311911705535	Metric
SCMT70554	9311911705542	Imperial



External Thread Files

- Restores damaged left or right-hand external threads, any diameter
- Ideal as a thread gauge
- Metric Thread Pitch: .80, 1.00, 1.25, 1.50, 1.75, 2.00, 2.50, 3.00
- Imperial UNC - UNF: TPI 11, 12, 13, 14, 15, 18, 20, 24

Part No.	Barcode	Type
SCMT70450	9311911704507	Metric
SCMT70449	9311911704491	Imperial



SCMT60000

Gas Soldering Iron

Barcode: 9311927600008

- 4 FUNCTIONS IN 1 TOOL
- Rechargeable with butane gas.
- Integrated ignition mechanism.
- Adjustable power.
- Complies with safety standards.
- Maximum temperature 1300 c.
- Per-heating time: 40 seconds
- Autonomy: 45 minutes.
- Power 10 to 75 watts
- Made in Ireland



SCMT70457

Tip Cleaning Set

Barcode: 9311911704576

- 12 drill sizes: 0.57mm – 1.61mm
- Magnetic cap stores drills in body
- Drills carburettor jets, circuit boards & oxy cutting tips.
- Magnetic pick-up in handle allows for quick pickup of drill bits

