

## Datasheet

### Crimp Tool for Ferrules

RS Stock number: 683-1614



#### Specifications:

- Non slip main handle and low friction moving handle ensure a comfortable hand grip
- Provides two-hand grip in the final phase of crimping, increasing comfort and productivity
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear mis-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Each tool has a unique serial number for traceability
- Durable: life span exceeds 50,000 cycles
- High strength, through hardened alloy Swedish steel construction

Crimp nest:	10.0 mm <sup>2</sup> / AWG 8 16.0 mm <sup>2</sup> / AWG 6 25 mm <sup>2</sup> / AWG 4
Wire size:	10.0-25 mm <sup>2</sup> / AWG 8-4
Connector:	Uninsulated and Insulated Ferrules
Description:	For ferrules, both uninsulated and insulated
Crimp profile:	Trapez-Crimp
Length:	230 mm/9.06"
Width:	21 mm/0.83"
Height:	70 mm/2.76"
Weight:	540 g/1.19 lb
Life span, cycles:	50,000