



ENGLISH

Product Datasheet

HSS DIN338 Fully Ground Drill



Material: HSS

Standard: DIN338

Point Angle: 118°

Surface: Surface: 0.25mm~0.95mm: bright finish; 1.05mm~1.75mm: black finish

Package: 5pcs in a plastic tube

Product Details:

RS Art.No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
7877315	0.25	19	3
7877327	0.30	19	3
7877324	0.35	19	4
7877330	0.40	20	5
7877321	0.45	20	5
7877337	0.50	22	6
7877333	0.55	24	7
7877349	0.60	24	7
7877346	0.65	26	8
7877352	0.70	28	9
7877343	0.75	28	9
7877359	0.80	30	10
7877355	0.85	30	10
7877361	0.90	32	11
7877368	0.95	32	11
7877365	1.05	34	12
7877374	1.10	36	14
7877377	1.25	38	16
7884984	1.65	43	20
7884987	1.75	46	22