

Features

- Ideal for heavy-duty or corrosion-prone environments.
- Allows free movement and is not self-closing.

RS PRO Hinges

RS Stock No.: 0726447



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a polished stainless-steel hinge (60×60 mm) with a 180° opening. It's screw-fixed on both the door and frame, features a captive pin, and is ideal for heavy-duty or corrosion-prone environments. It allows free movement and is not self-closing

General Specifications

Material	Stainless Steel (AISI 316)
Hinges Type	Screw-on
Closing Type	Free movement
Fixing Method	Screws
Pin Style	Fixed
Finish	Polished
Handed	Left; Right
Colour	Metallic
Applications	Single / In-line cabinets with single or double door

Mechanical Specifications

Length	60mm
Width	60mm
Thickness	8mm
Fixing Hole Sizes	8.4mm
Radial Load	3200 N
Axial Load	3800 N
Recommended Tightening Torque	5 Nm
Weight	186g
Pin Thickness	8mm
Knuckle Diameter	15mm
Pin Diameter	8mm
Opening Angle	180°
Screw Gauge	M8
Fixing Centres	36mm