



Part Number : [152670203](#)

Product Description : 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 51.00mm Cable Length, Tin (Sn) Plating, 6 Circuits

Series Number : 15267

Status : Active

Product Category : Flat-Flexible Cable (FFC)



Documents & Resources

Drawings

[152670203 sd.pdf](#)

Specifications

[PS-15267-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15267
Description	1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 51.00mm Cable Length, Tin (Sn) Plating, 6 Circuits
Comments	Contacts on the same side, Type A
Product Name	Premo-Flex FFC Jumper
UPC	884982439757

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Physical

Cable Length	51.00mm
Circuits (Loaded)	6
Contact Layout Type	A (same side)
Design Feature	Flexible
Flammability	94V-0
Material - Plating Mating	Tin
Net Weight	0.245/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm

Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 6 Circuits, Tin-Bismuth Plating	<u>522710679</u>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 6 Circuits, Tin-Bismuth Plating	<u>526100671</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 6 Circuits	<u>528080670</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 6 Circuits	<u>528080671</u>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 6 Circuits, Tin-Bismuth Plating	<u>522070685</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 6 Circuits	<u>527930670</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 6 Circuits	<u>528060610</u>
1.00mm Pitch Easy-On FFC/FPC	<u>528070610</u>

Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 6 Circuits	
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 6 Circuits	<u>528520670</u>