Technical sheet

TPX273NJ

Corner protection flexible bollard – Ø270 x 1000 mm – with plate – yellow/black

Flexible memory-shape safety post with a 1000mm diameter and a flat head, designed to prevent damage to vehicles and equipment. In case of impact, the bollard deforms and then returns to its original shape without breaking the anchoring or mounting. It is resistant to tearing, pulling, and breaking. Typically used for separating and protecting different areas in warehouses, it is directly anchored into the ground. Various options available, including chain rings and mounting hardware.







Customs code	3926909790
EAN	3321360109965

Color : Red/White

Material : Polyurethane

Specifications :

- Corner protection flexible post.
- Allows you to protect corners, avoids shocks to your installations and vehicles.
- To be fixed directly into the ground: 3 fixing holes ref TPUFIX1SB (optional) Indoor/outdoor use.
- Corrosion resistant.
- Resists temperatures between - 20°/+50°C.

Width (mm)	Height (mm)	Diameter post (mm)	Number of fasteners	Net weight (kg)
370	1000	270	3	7,90

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France

Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com