





LSZH Speaker cables

Belden Speaker cables use OFHC conductors offer Top Performance.

Top range of speaker cables complying to the CPR Euroclass requirements up to B2ca.



Belden LSZH OFHC Speaker cables answer the need for an CPR Euroclass rated, high-end speaker cable with distinct performance and installation benefits.



Enhanced Sound Performance

The copper conductors of Brilliance Low Cap OFHC Speaker cable have been manufactured using an upright shaft manufacturing process. The result of this process is a high-conductivity copper conductor that is inherently free of impurities.

Construction details

The range of products consists of 2 x 1.5 mm², 2 x 2.5mm², 4 x 2.5mm² and 2 x 4.0 mm². These are available in CPR Euroclass ratings:

- B2ca-s1,d1,a1
- Cca-s1,d1,a1
- Dca-s2,d2,a1




Euroclass program

Euroclasses are uniform assessment methods or classifications that reflect real-life environments for building products based on reaction-to-fire performance. Based on the cable's performance, it is placed into the Euroclass system that indicates its behavior during a fire.

The Euroclass program provides rankings based on the following criteria:

- Contribution to expanding a fire (rating from "no contribution" to "high contribution," with several levels in between)
- Smoke production development (rating from "limited production" to "strong production")
- Burning falling particles/droplets (rating from "no" to "high")
- Class corrosiveness/acidity of combustion gases (ranging from "low corrosiveness" to "high corrosiveness")



Description	Part No.	Euroclass	No. of Cond.	Standard Lengths [m]	Standard Weight [kg]	Diameter over Insulation [mm]	DC Resistance conductor [Ω /km]	Nominal O.D. [mm]
-------------	----------	-----------	--------------	----------------------	----------------------	-------------------------------	---	-------------------

1.5 mm² Stranded (30 x 0.25mm²) Conductors | Oxygen-free Bare Copper | Conductors Cables

LSZH Insulation | LSZH Jacket

Red and Black cores



70045	Dca-s2,d2,a1	2	100	62.1	2.3	< 13	6.3
			250				
			500				
70045LW	Cca-s1,d1,a1	2	100	72.6	2.3	< 13	6.8
			250				
			500				
70045LV	B2ca-s1,d1,a1	2	100	72.6	2.3	< 13	6.8
			250				
			500				

2.5 mm² Stranded (50 x 0.25mm²) Conductors | Oxygen-free Bare Copper | Conductors Cables

LSZH Insulation | LSZH Jacket

Red and Black cores



70046	Dca-s2,d2,a1	2	100	2.7	< 8	7.3
			250			
			500			
70046LW	Cca-s1,d1,a1	2	100	2.7	< 8	8
			250			
			500			
70046LV	B2ca-s1,d1,a1	2	100	2.7	< 8	8
			250			
			500			
70047	Dca-s2,d2,a1	4	100	2.7	< 8	8.5
			250			
			500			
70047LW	Cca-s1,d1,a1	4	100	2.7	< 8	9.5
			250			
			500			
70047LV	B2ca-s1,d1,a1	4	100	2.7	< 8	9.5
			250			
			500			



4 mm² Stranded (56 x 0.3mm²) Conductors | Oxygen-free Bare Copper | Conductors Cables

LSZH Insulation | LSZH Jacket

Red and Black cores



70048	Dca-s2,d2,a1	2	100	3.3	< 4.5	8.6
			250			
			500			
70048LW	Cca-s1,d1,a1	2	100	3.3	< 4.5	8.6
			250			
			500			
70048LV	B2ca-s1,d1,a1	2	100	3.3	< 4.5	8.6
			250			
			500			