

FEATURES

- Provides quick and easy connection and disconnection
- Fully Insulated for protection against electrical shock
- Double crimp design with an internal copper sleeve
- Tin plating for resistance to corrosion
- Colour coded insulation for easy identification

RS PRO Blue Insulated Spade Connector, 6.3 x 0.8mm Tab Size, 1.5mm² to 2.5mm²

RS Stock No.: 534-705



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Spade Connectors



Product Description

From RS PRO a high-quality insulated crimp receptacle terminal sometimes known as a female quick disconnect. Female crimp receptacles are a type of electrical wiring connector which, when mated with a male tab connector (or male quick disconnect), provide a fast and reliable interconnect between two wires. The body of the connector is made from tin plated brass and features an additional internal copper sleeve. This copper sleeve strengthens the barrel and provides a robust and secure crimp. The sleeve also protects the wire against stress and high vibration. The receptacle also has a plastic insulation which provides protection against electric shock and offers protection from dirt, grease, liquids and other contaminants. The colour of the insulation matches the wire size that the connector is used with making identification quick and easy.

General Specifications

Insulation	Insulated
Insulation Material	Vinyl
Termination Method	Crimp
Contact Plating	Tin
Contact Material	Brass
Colour	Blue
Applications	Industrial control systems; Industrial machines; Automotive applications; Communication equipment; Power supplies; HVAC; Domestic appliances including dishwashers, washing machines and dryers
Gender	Female
Shrouded/Unshrouded	Shrouded

Mechanical Specifications

Minimum Wire Size	1.5mm²
Maximum Wire Size	2.5mm²
Tab Size	6.3mm x 0.8mm
Minimum Wire Size (AWG)	14AWG
Maximum Wire Size (AWG)	16AWG
Overall Length	21.5mm

Spade Connectors



Approvals

Compliance/Certifications	UL Listed

Spade Connectors







Conversion table			
M3 / 6 BA	M5/ 2BA		
M3.5/ 4BA	M6/ 0BA		
M4/ 3BA			

Wire Sizes		
Mini Yellow	0.2 - 0.5 mm ²	
Red	0.5 - 1.5 mm²	
Blue	1.5 - 2.5 mm²	
Yellow	2.5 - 6.5 mm ²	

Technical Specification		
Temperature rating	+70°C	
Body Material	Copper	
Body Plating	Tin	