

PRODUCT-DETAILS

TY234M

CABLE TIE 18LB 14IN NATURAL NYLON



General Information

Extended Product Type	TY234M
Product ID	7TAG009050R0000
EAN	5414363061557
Catalog Description	CABLE TIE 18LB 14IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 357mm (14 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1.1mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

Ordering

EAN	5414363061557
UPC	786210830704

Dimensions

Product Net Width	0.1 in 2.54 mm
Product Net Depth / Length	14 in 355.6 mm

Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 2 Units	10000 piece
Package Level 2 Width	11.75 in 298 mm
Package Level 2 Height	9.75 in 248 mm
Package Level 2 Depth / Length	20.3 in 516 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19710405
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000570
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY234M
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

