

## Rexel Momentum X420 Cross Cut Paper Shredder

The power to shred more! The Momentum X420 paper shredder shreds up to 20 sheets (80 gsm) in to P-4 (4x40mm) cross cut pieces, with a 30L bin which holds 275 A4 sheets.



## Attributes

- Shreds up to 20 sheets in one pass (80gsm)
- P-4 (4x40mm), 1 x A4 sheet into 400 cross cut pieces
- 30L bin capacity, 275 A4 sheets
- Anti jam technology, shredder automatically stops and reverses when too much paper is inserted
- Easily shreds multiple documents, even with staples and paperclips on the corners
- Sleep mode after 2 minutes of non use
- Bin full indicator
- Ultra quiet operation < 60 DbA
- Touch panel operation for easy use
- 2 Year Warranty
- 2 Year Cutter Warranty



## Specifications

Number	2104578
Colour	black
Dimensions (W x H x D)	406 x 594 x 320 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	230
Run Time From Cold (min)	240
Run Time/Cool Down Time (min)	240/60
Shredded Particle Width mm	4x40
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	22
Cutting Capacity sheets (80gsm paper)	20
Container/collection volume in l	30
Shreds	Paper, Paper clips & Staples
Power consumption (W)	450
Noise Level (dBA)	58
Period of Warranty (Years)	2
Weight	22000 g
Pallet quantity	12
EAN code	5028252523394