

PRODUCT-DETAILS

TC345A

4WAYADH MTG BASE 1.1X1.1IN NAT NYL



General Information

Extended Product Type	TC345A
Product ID	7TAG009820R0045
EAN	5414363058564
Catalog Description	4WAYADH MTG BASE 1.1X1.1IN NAT NYL
Long Description	Four-Way Adhesive Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.7mm (0.22 Inches), Self-Adhesive Mounting Method, Bulk Pack

Ordering

E-Number (Finland)	1381498
EAN	5414363058564
UPC	786210868042

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	14 in 356 mm
Package Level 1 Depth / Length	20 in 508 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	9.89 in 251 mm

Package Level 2 Height	13.7 in 348 mm
Package Level 2 Depth / Length	21 in 533 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19731207
Material	Nylon/Polyamide 6.6
Mounting Holes	#6
Mounting Type	Self-Adhesive
Number of Batteries	0
Number of Entrances	4
Process Temperature Rating	-32 to +150 °F
Product Name	NYLON CABLE TIE MOUNTING BASE
Product Type	Mounting Base
Special Functions	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC345A
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC345A
RoHS Information	9AKK107991A8070

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

