



SIRIUS CABLE-OPER. SWITCH METAL HOUSING,1X M16X1.5 1NO+1NC, LATCHES AC.EN ISO13850 BUTTON RESET WITH LED-LAMP 24VDC, RED

### General technical details:

product designation		cable-operated switch
Supply voltage	V	24 ... 24
Number of indicator lights		1
Type of unlocking device		push-to-unlatch mechanism
Rope length / maximum	m	50
Product component / EMERGENCY STOP device		Yes
Item designation / according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Item designation / according to DIN EN 61346-2		S
Width	mm	166
Height	mm	105
Depth	mm	88

### Enclosure:

Type of mounting		screw fixing
material / of the housing		metal
Color / of the top part of housing		grey

### Contact:

Number of NC contacts / for auxiliary contacts		1
--	--	---

Number of NO contacts / for auxiliary contacts	1
Switching function / arresting lock	Yes

**Certificates/approvals:**

**General Product Approval**      **Declaration of Conformity**



CSA

GOST

EG-Konf.

**Shipping Approval**      **other**



ABS

BUREAU  
VERITAS

LRS

PRS

RINA

[Confirmation](#)

**Ambient conditions:**

Protection class IP	IP65
Ambient temperature • during operating	°C -25 ... +70

**Further information:**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrial-controls/mall>

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3SE7140-1BD04/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3SE7140-1BD04](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SE7140-1BD04)

**last change:**

Apr 30, 2012