

## Features

- 94mm cubic-design LED steady/flashing beacon with built-in buzzer indicator
- Steady and flashing light can be switched externally
- Beacon with good frontal and lateral signalling effect
- Beacon with 30cd luminous intensity
- Buzzer indicator provides 80dB (A) sound pressure
- High degree of protection IP65
- Optional mounting type using metal bracket
- 230-240V AC supply voltage

## RS PRO Beacons

**Auer Signal: 0694317**



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- 94mm cubic-design LED steady/flashing beacon with built-in buzzer indicator.
- Steady and flashing light can be switched externally.
- 16 LED light sources with a service life light source of >50,000 hours
- Ideal frontal and lateral signalling effect
- Buzzer max. 80 dB (A) sound pressure with a tone frequency of 3.5kHz
- 2 tones available that can be switched externally, steady tone or pulsing tone.
- Beacon with good frontal/lateral signalling effect
- Can be mounted directly on walls horizontally or vertically.
- Offers a high degree of protection (IP65) with a IK07 impact resistant rating.
- For industrial, plant construction, logistics and general applications
- Full mounting accessory package available

## General Specifications

|                                 |                                                                                       |
|---------------------------------|---------------------------------------------------------------------------------------|
| <b>Lens</b>                     | Polycarbonate                                                                         |
| <b>Nominal flash rate</b>       | 1.4 Hz                                                                                |
| <b>Bulb Type</b>                | LED                                                                                   |
| <b>Light Effect</b>             | Strobe/Flashing                                                                       |
| <b>Lens Colour</b>              | Red. Polycarbonate, ribbed inside                                                     |
| <b>Fitting</b>                  | 4 bolt                                                                                |
| <b>Flash Pattern</b>            | Single                                                                                |
| <b>Housing Colour</b>           | Red.                                                                                  |
| <b>Lamp Include</b>             | Yes                                                                                   |
| <b>Multifunction</b>            | Yes                                                                                   |
| <b>Number of flash patterns</b> | 2                                                                                     |
| <b>Number of LED</b>            | 16                                                                                    |
| <b>Special Features</b>         | Buzzer volume: 80db<br>2 Tones: Steady tone or Pulsing tone<br>Tone frequency: 3.5kHz |
| <b>Protection</b>               | Against water & dust, vibration (IK07)                                                |

## Electrical Specifications

|                            |                |
|----------------------------|----------------|
| <b>Supply Voltage</b>      | 230-240V AC/DC |
| <b>Light Output</b>        | 30 Cd          |
| <b>Current Type</b>        | AC/DC          |
| <b>Current Consumption</b> | 110mA          |

## Mechanical Specifications

|                       |                                |
|-----------------------|--------------------------------|
| <b>Dimensions</b>     | 94mm (w) x 99mm (d) x 94mm (h) |
| <b>Base Diameter</b>  | 94mm                           |
| <b>Base Length</b>    | 99mm                           |
| <b>Base Width</b>     | 94mm                           |
| <b>Mounting Style</b> | Screw Mount                    |
| <b>Weight</b>         | 300g                           |

## Operation Environment Specifications

|                            |       |
|----------------------------|-------|
| <b>Maximum Temperature</b> | +60°C |
| <b>Minimum Temperature</b> | -30°C |

## Protection Category

|                  |      |
|------------------|------|
| <b>IP Rating</b> | IP65 |
|------------------|------|

## Approvals

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Compliance/Certifications</b>    | CE / UL                |
| <b>Declarations</b>                 | RoHS Compliant / REACH |
| <b>Standards Met</b>                | Yes                    |
| <b>Hazardous Area Certification</b> | N/A                    |

