

Features

- Corrosion-resistant screws
- Easy wiring installation
- Phenolic body
- Zinc-plated steel terminal screws

RS PRO Term Strip Barrier 8Poles 15A 300V Phenolic

RS Stock No.: 0458763



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

From RS PRO, this non-fused terminal block presents a reliable and cost-effective solution to wire to-wire connections. This lightweight and robust terminal block is designed for free hanging or panel mount applications.

General Specifications

Fused	NO
Mounting Type	Free Hanging, Panel Mount
Contact Material	Brass
Termination Method	SCREW
Material	Phenolic
Number of Ways	8

Mechanical Specifications

Optional cable size	22~14AWG
Suggested screw torque	9Ib.-in.
Operating Temperature	150°C maximum

Electrical Specifications

Voltage Rating	300VAC RMS maximum
Current Rating	15A Amps maximum

Approvals

Standards Met	UL Recognized
Declarations	CE/UKCA Declaration of Conformity

DIMENSION

