



ANSMANN Work Light IL300R

- Professional work light with latest SMD LED technology
- Additional spotlight in lamp head
- Robust plastic housing with rubberized surface
- 180° rotatable lamp handle, (in 8 steps), for flexible lighting alignment
- Two foldable and 360° rotatable hooks at the back
- Two magnets on the back of the housing and one magnet on the bottom of the handle
- Impact protected Li-Ion battery pack (3.7V / 2200mAh)
- Charging via Micro USB (cable supplied)
- Charge control indication via dual colour LED
- Illumination 555 Lux / 1m
- Luminous flux 325 Lumens (main light) / 110 Lumens (additional spotlight)
- Lighting duration approx. 3,5 hours / 9 hours
- Charging time: approx. 3.25 hours
- 2 years ANSMANN Germany warranty

INFORMATION

Product name: IL300R
Article number: 1600-0152
EAN-Code: 4013674106004
Accessories incl.: USB charge cable
Product: 274x64x40mm / 282g
Packing + product: 390x125x51mm / 459g

Packing unit: 6 (335x270x140mm)
Customs tariff number: 85131000
Material group: 02

