



M18 Compact Metal Shear

M18 BMS20-0

- 360° Tool-Free Rotating Head
- Ergonomic Body Design
- Variable Speed Trigger

MODEL VARIANT



INCLUDES

- M18 BMS20-0 (1)
- Belt Clip (1)
- Hex Key (1)

PRODUCT SPECIFICATIONS

Length (mm)	432
Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
FUEL Gauge	Yes
LED Light	No
No Load Speed (rpm)	0 - 2500
Max. aluminum wire capacity (mm ²)	3.2
Max. cutting capacity steel (mm)	2
Minimum cutting radius (mm)	180
Weight with battery pack if applicable (kg)	2.6