


## 30.5mm Panel Mount Components

### Certification Information

- \* Certification Number PTB99ATEX1034
- \* Approved to  II 2G EEx de IIC T6
- \* Ingress Protection IP66
- \* Ambient Temperature Range -20°C to +40°C

### Features

- \* Contact blocks fitted to actuator by way of a bayonet catch
- \* Rated up to 500V AC at 16A on pushbuttons & mini switches
- \* Silver contacts as standard
- \* Suitable for a wall thickness of up to 5mm
- \* Cables must be terminated in an approved enclosure

- \* **Must be fitted with protective cap to comply with certificate**



### Push Buttons



Part Number	Function	Contacts	Action
GHG4188115R0001	Push Button	1 N/O + 1 N/C	Momentary
GHG4188125R0001	Key Operated Push Button	1 N/O + 1 N/O	
GHG4188145R0001	Double Push Button	1 N/O + 1 N/C	
GHG4188153R1200	Emergency Stop	2 N/C	Pull to Reset
GHG4188155R1200	Emergency Stop	1 N/O + 1 N/C	
GHG4188155R1300	Key Emergency Stop	1 N/O + 1 N/C	Key to Reset

### Selector & Key Switches



Part Number	Function	Contacts	Action
GHG4188190R5307	3 Position (I-0-II)	2 N/O	Maintained
GHG4188190R6102	2 Position (I-II)	1 N/O + 1 N/C	
GHG4188190R6201	2 Position (0-I)	2 N/O	
GHG4188195R5507	3 Position (I-0-II)	2 N/O	Key Operated

### Signal Lamps



Part Number	Function	Voltage	Colour
GHG4188170R0051	Signal Lamp	20 - 250V AC/DC	Supplied with red, green, amber & white lenses
GHG4188170R0053		12 - 30V AC/DC	

### Potentiometers



Part Number	Function	Voltage	Action
GHG4188131R0016	10 kΩ Potentiometer	250V AC/1W	Rotary

### Accessories



Part Number	Description
GHG4101939R0002	Rear Terminal Protective Cap
GHG4101901R0125	Flap Bracket
GHG4101901R0126	Padlockable Bracket