



Cordless Outdoor
Cleaners

Fontus

Freedom to clean. Anywhere,
any time.

[Go to product](#)



Key product features

- Mobile cleaning at home or on the go, independent of mains water or electricity supply
- Fast set-up and easy manoeuvrability for quick and effortless results
- Multipurpose use: Four spray patterns, adjustable water pressure, and SmartBrush

Other product advantages

- 15 L integrated water tank is ideal for washing bikes, garden furniture, dogs and boots
- Extendable handle, sturdy wheels, and accessory storage for ultimate convenience
- One battery fits all – suitable for all DIY and garden tools in the Power for ALL lithium-ion cordless systems
- Syneon Chip – Intelligently controlled energy for every project

Comes complete with

- Spray gun
- 4 m hose
- Water filter
- SmartBrush
- Charger AL 1815 CV
- 1 battery pack PBA 18V 2.5Ah W-B

Part number: 06008B6070

EAN code: 3165140909105



Cordless Outdoor Cleaners

Fontus

Technical data

Max. pressure: 15 bar

Pressure settings: low, medium and turbo

Flow range, from: 1,5 l/min

Flow range, to: 3,1 l/min

Flow range: 1,5 - 3,1 l/min

Battery voltage: 18 V

Battery capacity: 2,5 Ah

Battery run time: up to 60 mins

Battery charging time: 105 min

Tank size: 15 l

Hose length: 4 m

Weight (without accessories): 9,8 kg

Height: 645 mm

Width: 395 mm

Depth: 320 mm

Product dimensions (HxWxD): 645 x 395 x 320 mm

Noise / vibration information

Measured values determined according to EN 60335
Total vibration values (vector sum of three directions).

Vibration emission value ah: 0.0 m/s²

Uncertainty K: 1.5 m/s²

Measured values for noise determined according to 2000/14/EC. The A-rated noise level of the power tool is typically as follows: Sound pressure level 61 dB(A); Sound power level 74 dB(A). Uncertainty K= 3 dB.

Functions



Battery voltage

18 volts

Functions

Ready to use out of the box

Storage for all accessories/hose/cables

Simple, quick connect fittings

Safe in-use gun storage

Water filter

Telescopic handle