

Base reinforcement H: 100 mm W: 850 mm



Model	
product brand name	SIVACON S4
product designation	Base reinforcement
design of the product	height 100 mm
design of cabinet base element	for standard frame
Suitability	
suitability for interaction cable assignment	No
suitability for use for outside use	No
Appearance	
RAL color number	Other
color	miscellaneous
product component	module incl. mounting material
• on delivery	
• ventilation	No
Mechanical Design	
height	100 mm
width	850 mm
depth	25 mm
installation width for cabinet installation	850 mm
installation depth for cabinet installation	850 mm
net weight	5.2 kg
material	sheet-steel
material thickness	2.5 mm
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ1010-0BA07>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ1010-0BA07>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ1010-0BA07

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/26/2025 

