

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under moving loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling significant stationary loads.
- **Flanged Design:** Facilitates easy installation and alignment.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards.
- **UKAS 001 Approved:** Ensures compliance with UK accreditation standards.

RS PRO 12.02 mm Flanged Plain Bearing

RS Stock No: 528-059



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under both dynamic and static loads. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for various industrial settings.

General Specifications

Bore Size	12.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	17.04 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------