

**ZMA70/110** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M70X2	Thread
D	110 mm	Outside diameter
h	35 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	810,000 N	Breaking load, axial
M _L	220 Nm	Breakawag
M _{AL}	130 Nm	Mounting torque reference
M _M	33 kg*cm ²	Mass moment of inertia
≈m	1.513 kg	Weight

Dimensions

d ₁	102 mm	Plant diameter outside
t	3.5 mm	Hight retaining slot
b	8 mm	Width retaining slot
c	17.5 mm	Distance bore
m	M8	Threaded - threaded pin