

## TROLLEYS AND SERVERS

### Options and accessories



**Plastic briefcase - 802 000 001**

Sticker

Compatibility: Trolleys fitted with pvc panels (container trolleys, constant level trolleys and modular trolleys), desks, models with door units and 4 drawers.



**A4 portrait document case - 882 006 150**

Sheet metal document holder. Dimensions 330 x 230 x 140 mm.

Compatibility: All models except those with plastic trays.



**A3 landscape document case - 802 000 010**

Sheet metal document holder with clamp. Secured by a steel collar on the handle.

Compatibility: All models except those with plastic trays.



**Shower holder - 882 006 149**

Dimensions 205 x 170 x 130 mm.

Compatibility: All models except those with plastic trays.



**Dispenser for rolls - 882 006 152**

For rolls Ø 300 mm max.

Compatibility: All models except those with plastic trays.



**Wire basket - 802 000 002**

Dimensions 500 x 150 x 200 mm

Compatibility: All models



**Sheet metal basket with integrated bottle holder - 882 009 529**

Tool box and integrated bottle holder. Allows the operator to carry accessories in a sheet metal box measuring 280 x 80 x 70 mm and to hold a 25 cl to 1.5 L water bottle.

Compatibility: All models



**Support net - 825 009 648**

Ideal for holding small loads. Fitted with 8 removable hooks. Quickly positioned around loads for excellent support.

Compatibility: All models



### Plastic bin

Dimensions: 400 × 300 × 120 mm, 14.4 L - 802 006 764

Dimensions: 600 × 400 × 120 mm, 28.8 L - 802 006 765

Dimensions: 600 × 400 × 235 mm, 56.4 L - 802 006 766

Dimensions: 600 × 400 × 320 mm, 76.8 L - 802 006 767

Compatibility: All models



### Handling sheaths - 802 008 420

Make it easier to handle trolleys and trolley trolleys.

Compatibility: For base L 1200 x 800 mm



### Support bar

For XS and S trays, width 500 mm - 802 000 017

For M tray, width 600 mm - 802 000 018

For tray L, width 800 mm - 802 000 019

Compatibility: FLATPACK™ and EVERSTEEL™ forklifts and servers.



### Desk-top desk with lockable writing tablet - 882 006 039

Dimensions: 440 × 520 mm.

Compatibility: All models



### Drawbar with spring return - 862 010 593

Easy truck handling. Drawbar held in vertical position by spring return.

Compatibility: Modular forklift trucks, container forklift trucks, pallet rollers, wire servo trolleys



### Galvanized sheet metal top, 25/10th thick

1060 x 680 mm - 882 006 147

1300 x 800 mm - 882 006 148

Compatibility: 500 kg bench-mounted trolleys



### Hand protection - 882 009 481

Protects hands from risk of crushing or shearing when handling parts for assembly. Sold individually.

Compatibility: Established servers

### Particularly scratch-resistant epoxy paint.

Standard colours at no extra cost, with 2 weeks lead time.

-  BLUE 5007
-  DARK GREY 7024
-  WHITE 9005
-  LIGHT GREY 7035
-  YELLOW 1003
-  SPECIFIC RAL On quotation
-  RED 3002



### Medium wood tray + non-slip rubber mat

Extra-thick matting to protect the wooden tray over time, protect the loads being transported and provide excellent soundproofing.

Tray XS, 550 x 500 mm - 802 006 705

Tray 720 x 450 mm - 802 006 702

Tray S, 850 x 500 mm - 802 006 706

Tray M, 1000 x 600 mm - 802 006 704

Tray L, 1200 x 800 mm - 802 006 740

Compatibility: Trolleys and servers



**Additional melamine-coated wooden top**  
16 mm thick, easy maintenance.

For XS tray, 550 x 500 mm - 882 701 008

For 700 x 600 mm tray - 882 701 014

For S tray, 850 x 500 mm - 882 701 011

For M tray, 1000 x 600 mm - 882 701 017

Compatibility : FLATPACK™ 250 kg Servantes



**Additional tray in medium wood**

16 mm thick, highly resistant to repeated impacts, it will not crack or splinter.

For XS tray, 550 x 500 mm - 882 701 007

For 700 x 600 mm tray - 882 701 013

For 815 x 750 mm tray - 882 701 019

For S tray, 850 x 500 mm - 882 701 010

For M tray, 1000 x 600 mm - 882 701 016

For tray L, 1200 x 800 mm - 882 701 021

Compatibility : 400 kg FLATPACK™ Servers



**Additional tray in galvanised sheet metal**

16 mm thick, reversible (face with or without 16 mm flange), 2 mm thick, suitable for corrosive environments.

For XS tray, 550 x 500 mm - 882 701 009

For 700 x 600 mm tray - 882 701 015

For 815 x 750 mm tray - 882 701 020

For S tray, 850 x 500 mm - 882 701 012

For M tray, 1000 x 600 mm - 882 701 018

For tray L, 1200 x 800 mm - 882 701 022

Compatibility: FLATPACK™ 250 - 400 kg forklifts



**Additional melamine-coated wooden top**  
16 mm thick, easy maintenance.

For S tray, 850 x 500 mm - 882 701 024

For M tray, 1000 x 600 mm - 882 701 028

Compatibility: EVERSTEEL™ 250 kg Servers



**Additional tray in medium wood**

16 mm thick, highly resistant to repeated impacts, it will not crack or splinter.

For M tray, 1000 x 600 mm - 882 701 027

For tray L, 1200 x 800 mm - 882 701 031

Compatibility: EVERSTEEL™ 400 kg Servers



**Additional tray in galvanised sheet metal**

2 mm thick, reversible (face with or without 16 mm lip), suitable for corrosive environments.

For S tray, 850 x 500 mm - 882 701 025

For M tray, 1000 x 600 mm - 882 701 029

For tray L, 1200 x 800 mm - 882 701 032

Compatibility: EVERSTEEL™ 250-400 kg Servers



**Additional galvanised steel tray + regenerated rubber mat**

2 mm thick sheet metal suitable for corrosive environments, easy to clean, with 16 mm lip. Recycled rubber mat, 10 mm thick, unglued for easy cleaning. Soundproof, resistant to chemicals and heat.

For S tray, 850 x 500 mm - 882 701 026

For M tray, 1000 x 600 mm - 882 701 030

For tray L, 1200 x 800 mm - 882 701 033

Compatibility: EVERSTEEL™ 250-400 kg Servers



#### Additional shelf, melamine-coated wood

Load capacity: 100 kg, 16 mm thick, easy maintenance.

For S tray, 850 x 500 mm - 882 701 001

For M tray, 1000 x 600 mm - 882 701 002

For tray L, 1200 x 800 mm - 882 701 003

Compatibility: EVERSTEEL™ multi-level and wire shelving units.



#### Additional sheet metal shelf

Load capacity: 100 kg, 2 mm thick, suitable for corrosive environments, easy maintenance, reversible (face with or without 16 mm lip).

For S tray, 850 x 500 mm - 882 701 004

For M tray, 1000 x 600 mm - 882 701 005

For tray L, 1200 x 800 mm - 882 701 006

Compatibility: EVERSTEEL™ multi-level and wire shelving units.



#### Additional push handle

Allows the trolley to be handled in 2 directions, ideal for confined spaces.

For 500 mm wide trays - 882 006 151

For 600 mm wide trays - 882 006 153

For 800 mm wide trays - 882 006 154

Compatibility: EVERSTEEL™ multi-level and wire shelving units.



#### Non-staining wheels

2 fixed + 2 swivel with brake. Start-up effort reduced by 50%. Quiet, non-staining TPE tyres.

Products fitted with 125 mm Ø castor wheels - 802 008 481

Products fitted with Ø 160 mm castors - 802 000 104

Products fitted with Ø 200 mm wheels - 802 000 108



#### Antistatic wheels

2 fixed + 2 swivel with brakes. Rubber tyres to prevent sparks.

Products fitted with 125 mm Ø castor wheels - 802 008 485

Products fitted with Ø 160 mm castors - 802 008 486

Products fitted with Ø 200 mm castors - 802 008 483



#### Non-staining swivel wheels

4 swivel castors with brakes. For 360° rotation on the spot.

Products fitted with 125 mm Ø castor wheels - 802 010 590

Products fitted with 160 mm Ø castor wheels - 802 010 591

Products fitted with Ø 200 mm wheels - 802 010 592



#### Swivel wheels

4 castors, 2 of which have brakes.

Products fitted with 125 mm Ø castor wheels - 802 008 479

Products fitted with Ø 160 mm castors - 802 000 109

Products fitted with Ø 200 mm wheels - 802 000 110



#### Wheels

2 fixed + 2 swivel with brake. Ideal for uneven or outdoor floors. Maximum load 250 kg.

Products fitted with Ø 160 mm castors - 802 000 113

Products fitted with Ø 200 mm wheels - 802 000 111