

Previously known as: Powerflex® 80-400



Cold



Heat



Medium Duty

Fleece-lined work gloves, ensuring safe and comfortable handling in cold conditions

- **Heightened visibility:** These safety gloves offer cut and abrasion protection in poor light conditions, with a seamless bright yellow terry loop acrylic liner
- **Reinforced grip:** ActivArm® 80-400 thermal gloves feature a bright blue crinkled palm finish, enhancing grip in wet and dry conditions
- **Optimized insulation:** Fleece-lined, with a natural latex coating, these thermal work gloves guard against temperatures as low as -15°C/5°F (extended contact) and -30°C/-22°F (intermittent/short contact), but are also able to handle hot components up to 250°C/480°F for 15 seconds
- **Advanced ergonomics:** ActivArm® 80-400 industrial gloves' ergonomic design grants users superior fit and comfort, while ensuring flexibility and dexterity



Industries

- Construction
- Forestry

Applications

- Shipping and loading of product
- Construction
- Outdoor Winter Use

Previously known as: Powerflex® 80-400

Key Features

- **Increased visibility design:** For personal protection in poorly lit environments
- **Crinkled palm coating:** Enhanced wet and dry grip
- **Fleece lining:** For assured low-temperature hand protection

Vulcanization Chemical Accelerators

- Dithiocarbamate
- Natural rubber proteins
- Zinc 2-mercaptobenzothiazole

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2231C

EN 407



X2XXXX

EN 511



020

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 80-400	Finishing: Palm Coated Coating Material: Natural Rubber Latex Liner Material: Acrylic Terry Loop Cuff Style: Knitwrist	7	7, 8, 9, 10, 11	250 - 290 mm, 10-12"	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.