



Datasheet

Stock No: 218-267

ENGLISH

RS Pro Interface Adapter Female D-sub, 9-Pin (Serial) to D-sub, 25-Pin Female D-sub, 25-Pin



Product Details

9-25 Way D Adaptors

9-25 way adaptors in various configurations to meet your requirements. These fully moulded adaptors can be used to match up peripheral units with different connector sizes quickly and easily. Durability of 100 mating cycles. 300V operating voltage. Screw posts (SP) and locking posts (LP) options on each connector (see price table for details).

Pin assignment								
D Sub 9	1	2	3	4	5	6	9	Shell
D Sub 25	8	3	2	20	7	6	22	Shell

Specifications:

Connector A	D-sub, 9-Pin (Serial) Female
Connector B	D-sub, 25-Pin Female
Connector A Gender	Female
Connector A Type	D-sub, 9-Pin (Serial)
Connector B Gender	Female
Connector B Type	D-sub, 25-Pin