
Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26KEIW21MPN
COUPLING HALF: Coupler
CONNECTION SIZE: G 1/2
FUNCTION: Self-Venting
BODY MATERIAL: Brass
CONNECTION TYPE: Female BSPP

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:
- General Industrial
- Industrial manufacturing equipment

Features/Benefits:
- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

INDUSTRY	General Industrial
MAXIMUM OPERATING PRESSURE	174 psi
FLOW RATE	830 L/min (air)
BRAND	Rectus
MAXIMUM OPERATING TEMPERATURE	140 °F
PRODUCT SERIES	Series 26
MAXIMUM OPERATING TEMPERATURE	60 °C
MINIMUM OPERATING TEMPERATURE	-4 °F
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
INDUSTRY	Transportation
MAXIMUM OPERATING PRESSURE	12 bar
DIVISION	Low Pressure Connectors Europe Division
WEIGHT	0.11 kg
CONNECTION SIZE	G 1/2
LENGTH	60 mm
INTERCHANGE TYPE	European Profile
COMPATIBLE FITTING	Series 25 Plug
DIAMETER	7.4 mm (nominal)
BRAND	Parker
MINIMUM OPERATING TEMPERATURE	-20 °C
INDUSTRY	Electronics
PRODUCT TYPE	Pneumatic Quick Couplings
FUNCTION	Self-Venting

OPERATION TYPE	Sleeve
APPLICATION	Electronics
TECHNOLOGY	Pneumatics
PRODUCT STYLE	Quick-Connect
CONNECTION TYPE	Female
BODY MATERIAL	Brass
HEX SIZE	24 mm
REGION OF ORIGIN	Germany
VALVE INCLUDED	Yes
APPLICATION	Energy Management
VALVE TYPE	Standard Valve
SEAL MATERIAL	NBR
CONNECTION TYPE	BSPP
APPLICATION	Air & Gas Compressor
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	5
COUPLING HALF	Coupler
APPLICATION	Trucks & Trailers
PLATING TYPE	Nickel-Plated
OUTSIDE DIAMETER	31 mm
APPLICATION	Mobile & Defence
SLEEVE MATERIAL	Brass