



Main

Commercial Status	Commercialised
Range of product	TeSys K
Device short name	LA4K
Product or component type	Suppressor module
Product compatibility	LC1 LP1

Complementary

Mounting location	Front side
Mounting mode	Clip-on
Suppressor technology	Bidirectional peak limiting diode
Control circuit voltage	12...24 V DC
Maximum peak voltage	2 Uc
Local signalling	LED
Quantity per set	Set of 5
Height	0.98 in (25 mm)
Width	0.24 in (6 mm)
Depth	0.87 in (22 mm)
Product weight	0.02 lb(US) (0.01 kg)

Environment

Standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TC conforming to DIN 50016 TC conforming to IEC 60068
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901833048
Nbr. of units in pkg.	5
Package weight(Lbs)	0.01
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	ID

Contractual warranty

Period	18 months
--------	-----------
