

**MNX PCM 125/60 T**



Sample photo

**Order symbol:** PCM 125/60 T  
**Product nbr:** 6016907  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074038203  
**El. number:**  
 Finland: 3421660  
 Denmark: 8212027077  
 Italy: 7342025  
 Sweden: 2535412  
 Norway: 2535508

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		130	130	60	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		5.1	5.1	2.4	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Cover screws material:</b>		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Cover screws colour:</b>		Black			NEMA Class: NEMA 1, 4, 4X, 6
<b>Gasket material:</b>		TPE			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C			Germanischer Lloyd (GL)
<b>Continuous:</b>		-40 ... 80 °C			Underwriters Laboratories
<b>Short term:</b>		-40 ... 250 °F			Det Norske Veritas
<b>Continuous:</b>		-40 ... 175 °F			Fimko
<b>Accessories:</b>					Europe EN 62208: 2003
MIV 125		Mounting plate (Galvanized steel)			UL Canada
MIN 10		DIN-15 Mounting rail			Gost R
MIV 10		DIN-35 Mounting rail			
FP A 125/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			

