



FLAMESTAT HIGH VIS CRAFTSMAN STRETCH TROUSERS WOMAN CLASS 1 2171 ATHF

ART. NO: 129521

Stretch material / Dirt, oil and water repellent / Concealed front button / 2 reinforced loose-hanging pockets, one with 3 small pockets and tool loops and one with extra pocket / 2 front pockets / 2 reinforced back pockets / Hammer loop / Double reinforced crotch seam / Reinforced pocket for folding rule and tools with pen pocket and button and loop for sheath knife / Leg pocket with flap and concealed snap fastening, mobile phone pocket and loop for ID-card holder / Reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / Metal free / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 8 cal/cm² (included in electric arc certified garment combinations), EN ISO 11612 A1 B1 C1 F1, EN 1149-5, EN ISO 20471 class 1 and EN 14404 together with kneepads 124292 / Fabric is approved according to EN 13034 / Certified after 50 washes / Laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: Stretch 45% modacrylic, 34% cotton, 17% polyamide, 2% elastane, 2% anti-static fibre. Reinforcement 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre. Inherent flame protection. In transition to PFAS free.

Weight: Stretch 265 g/m². Reinforcement 300 g/m².

Color: F171 High vis Yellow/Navy

Size: 34-50



PRO **T1**

EN 11612 EN 1149-5 IEC 61482-2 EN 20471 EN 14404

FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04