



## Armstrong 6.375 in Black Oxidized C Hook Wrench with 3/4 → 2in Jaw Capacity

### Features

- Incorporates One Adjustable Hook which is designed to Adjust Threaded Collars, Locknuts, Rings, Packing Nuts, in Industrial Applications.
- Manufactured From High Alloy Steel Using the Most Up-To-Date Manufacturing Process and Heat Treat for Greater Strength and Durability

### Specification

Finish	Black Oxidized
Maximum Jaw Capacity	2in
Minimum Jaw Capacity	3/4in
Overall Length	6 3/8 in