



WM626

Workmate® Dual Height Tough Workbench

Selling Proposition

- Dual working heights for use as a workbench, bench tool stand, vice, or sawhorse
- Durable steel frame construction
- Folds flat for compact storage and easy transport
- Heavyweight steel construction allows support of 250kg
- Dual clamping cranks increase clamping force and versatility
- Adjustable swivel pegs and jaw retention grooves provide clamping versatility and reliable material hold

Standard Equipment

- N/A

Warranty Specifications

- 2 Year Guarantee

Specifications	
Working heights	775 / 595 mm
Folded size (W x H x D)	742 x 740 x 200 mm
Vice jaw opening	0-136 mm
Vice jaw length	740 mm
Max table width - Jaws open	384 mm
Vice jaw positions	1
Maximum load	250 kg
Verticle clamping	No