

FBP-3F 4U - Blind plug



1029279

<https://www.phoenixcontact.com/in/products/1029279>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Blind plug, color: gray

Commercial data

Item number	1029279
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6
Product key	BE6114
Catalog page	Page 651 (C-1-2019)
GTIN	4055626531359
Weight per piece (including packing)	157.4 g
Weight per piece (excluding packing)	157.4 g
Customs tariff number	85389099
Country of origin	PL

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



Technical data

Product properties

Product type	Blind plug
--------------	------------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1029279>



CSA
Approval ID: 13631



cUL Recognized
Approval ID: FILE E 60425



UL Recognized
Approval ID: FILE E 60425

cULus Recognized

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-13.0	27250304
ECLASS-12.0	27440313

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	567f7905-dab1-4a5a-ba00-b928042245d1

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



Accessories

BTFE 6-3/14 4U - Test terminal strip

1029251

<https://www.phoenixcontact.com/in/products/1029251>



Test terminal strip, nom. voltage: 400 V, nominal current: 24 A, connection method: Ring cable lug, 1 level, Rated cross section: 6 mm², mounting type: Panel mounting, color: gray

BTFE 6-3/18 4U - Test terminal strip

1029255

<https://www.phoenixcontact.com/in/products/1029255>



Test terminal strip, nom. voltage: 400 V, nominal current: 24 A, connection method: Ring cable lug, 1 level, Rated cross section: 6 mm², mounting type: Panel mounting, color: gray

FBP-3F 4U - Blind plug

1029279

<https://www.phoenixcontact.com/in/products/1029279>



TMT (EX6,2)R - Marker for terminal blocks

0803063

<https://www.phoenixcontact.com/in/products/0803063>



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: latching, snap into flat marker groove, Number of individual labels: 1, text field height: 6.2 mm, text field width: 50000 mm

US-TMF 100 - Marker for terminal blocks

0829260

<https://www.phoenixcontact.com/in/products/0829260>



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, snap into flat marker groove, Number of individual labels: 20, text field height: 6.6 mm, text field width: 104 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in