

## ToLEDo GLS

ToLEDo GLS Dim V2 806LM 827 B22 SL

0026677



### Range features

- Wide beam angle of 220 degrees!
- Instant start
- Long lifetime 15,000 hours
- Short payback period
- Up to 85% energy savings compared to incandescent equivalent

LED

### PRODUCT OVERVIEW

Light colour	Homelight
Technology	LED
Ordering number	0026677
Average life (Rated) (h)	15000
Energy class	A+
Lamp shape	A60
Lamp finish	Frosted
Dimmable	Yes
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288266770
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Efficacy (Rated) (lm/w)	84.8
Watt (Nominal) (W)	9.5
Equivalent watt (W)	60
Voltage (V)	220-240
Colour	Homelight

# ToLEDo GLS

ToLEDo GLS Dim V2 806LM 827 B22 SL

**0026677**

## DATA TABLE

### General data

Dry applications use only	Yes
Technology	LED
Ordering number	0026677
Energy class	A+
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000
Energy saving lamp	Yes
Lamp finish	Frosted
Lamp shape	A60
Dimmable	Yes
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288266770
Range features	Wide beam angle of 220 degrees! Instant start. Long lifetime 15,000 hours. Short payback period. Up to 85% energy savings compared to incandescent equivalent
Product name	ToLEDo GLS Dim V2 806LM 827 B22 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Intended purpose	No
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

### Optical data

Light colour	Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	806
Adjustable chromaticity	No

## ToLEDo GLS

ToLEDo GLS Dim V2 806LM 827 B22 SL

**0026677**

### Electrical data

kWh per 1000 hours burning time	10
Efficacy (Rated) (lm/w)	84.8
Watt (Nominal) (W)	9.5
Watt (Rated) (W)	9.5
Equivalent watt (W)	60
Voltage (V)	220-240
Current (A)	47
Lamp power factor	0.9

### Physical data

Colour	Homelight
Lamp Length (mm) - C/L	108
Max. Lamp Diameter (mm) - D	60
Lamp dimension equal to filament lamp equivalent	Yes
Diameter (mm)	60

## ENERGY LABEL

